


Ideal for use in warehouses, manufacturing processes, and production facilities, the CCT bench counting scale is practical for any counting application. Quickly check the number of pieces in a carton or container, helping reduce waste when filling orders or packaging shipments. Intuitive software is user-friendly and keeps track of the count, automatically optimizing the unit weight for greater accuracy. The programmable backlit display can be customized to be “always on,” “always off” or to light only when weighing.

With easy operation and a durable design, Cruiser bench counting scales provide a powerful solution for industrial needs.



Features

- Backlit LCD shows weight, unit weight and count in one convenient location
- Color-coded keys facilitate quick recognition of the most frequently used buttons
- RS-232 interface is available to provide speedy connection to computers and printers
- Optional USB interface simplifies data communication
- Solid ABS housing is durable for industrial use
- Adjustable leveling feet help optimize setup
- Built-in memory for storing products and settings
- External calibration allows for verification and adjustment with weights
- Internal counting resolution 1:600,000 for precise results
- Parts counting optimization automatically refines piece weight as parts are added
- Parts counting with freely selectable sample sizes
- Preset tare function speeds the process of repetitive weighing
- Programmable for counting to a preset number of parts
- AC adapter included
- Programmable auto power-off to save energy
- Rechargeable battery included for operation almost anywhere

Applications

- Weighing
- Parts counting
- Check counting

About ADAM:

For more than 45 years, professionals worldwide have relied on Adam Equipment for an extensive selection of dependable and affordable weighing equipment. Adam provides the right balance of speed, performance and value.

Model	CCT 4	CCT 8	CCT 16	CCT 32	CCT 48	CCT 8UH	CCT 16UH	CCT 32UH	CCT 48UH
Capacity	8lb / 4kg	16lb / 8kg	35lb / 16kg	70lb / 32kg	100lb / 48kg	16lb / 8000g	35lb / 16kg	70lb / 32kg	100lb / 48kg
Readability	0.0002lb / 0.1g	0.0005lb / 0.2g	0.001lb / 0.5g	0.002lb / 1g	0.005lb / 2g	0.0001lb / 0.05g	0.0002lb / 0.1g	0.0005lb / 0.2g	0.001lb / 0.5g
Repeatability (S.D.)	0.0004lb / 0.2g	0.001lb / 0.4g	0.002lb / 1g	0.004lb / 2g	0.01lb / 4g	0.0002lb / 0.1g	0.0004lb / 0.2g	0.001lb / 0.4g	0.002lb / 1g
Linearity (+/-)	0.0006lb / 0.3g	0.001lb / 0.6g	0.003lb / 1.5g	0.006lb / 3g	0.01lb / 6g	0.0006lb / 0.3g	0.001lb / 0.6g	0.003lb / 1.2g	0.006lb / 3g
Pan Size	8.3"x11.8" / 210x300mm								
Weighing Units	g, kg, lb								
Stabilization Time (sec)	2								
Interface	RS-232, Optional USB								
Calibration	External calibration								
Display	Backlit LCD with 0.6" / 15mm -high digits								
Power Supply	12VDC 800mA adapter / Internal rechargeable battery								
Operating Temperature	-10° to 40°C / 14° to 104°F								
Housing	ABS plastic								
Overall Dim.	12.8"x14"x4.5" / 326x355x115mm (wxdxh)								
Net Weight	7.3lb / 3.29kg								

Accessories

Item number	Description
3022013912	Hard carrying case with lock
2020013913	In-use cover (pack of 5)
2020013914	In-use cover (pack of 10)
3022013911	In-use wet cover
3074010267	USB cable
3014011014	RS-232 cable M-F
1120014641	AIP impact printer
1120011156	ATP thermal printer
600002028	AdamDU Data Collection Program
202000001	Weigh-below hook (factory fitted)
700660290	Calibration certificate
2020013915	USB option

Key Accessories



ATP thermal printer

Easy-to-use features combined with quick set-up equals a truly versatile thermal printer. A single push-button feed key and three easy-to-read LED indicators make operation simple.



AdamDU data collection program

Adam DU software connects a balance to the laboratory network, helping to achieve seamless data collection, transfer and analysis. DU features an easy-to-use interface with a main command window, allowing users to quickly collect information from up to eight Adam balances simultaneously using RS-232 or USB connections.

Supplied by